CONTEG DATASHEET

FREE-STANDING RACKS

PREMIUM Housing RSB

CONTEG, spol. s r.o.

Czech Republic Headquarters:

Na Vítězné pláni 1719/4 140 00 Prague 4

Tel.: +420 261 219 182 Fax: +420 261 219 192

Production plant in the Czech Republic:

K Silu 2179 393 01 Pelhřimov

Tel.: +420 565 300 300 Fax: +420 565 533 955

Local Branches/Offices

Austria: +43 170 659 0115
Benelux: +32 477 957 126
Eastern Europe / Nordics: +49 172 8484 346
France, Maghreb: +33 686 074 386
Germany / Switzerland /
Baltics / Denmark / Italy: +49 170 523 4958

Baltics / Denmark / Italy: +49 170 523 4958 India: +91 99 1695 0773 Middle East: +971 4445 2838 Russia, CIS: +7 495 967 3840

conteg@conteg.com www.conteg.com

PREMIUM Housing RSB

The PREMIUM Housing RSB rack series is designed for server housing and co-location centers, where they can be installed as standalones or in rows. The rack can be designed with 2, 3 or 4 sections upon request. These compartments are equipped with individually adjustable 19" extrusions that can be individually locked and separated by perforated high-load shelves. Moreover, the rack can be equipped with individual cable guiding and a separation frame (must be ordered separately). All 19" types of active or passive equipment can be housed inside.



COLOR SAMPLER:

RAL 9005

RAL 7035

DESCRIPTION:

c:---

- Height: 42, 45, 48U (total useful height = 42/45/48 number of compartments)
- · Width: 600, 800 mm
- Depth: 800, 1000 and 1200 mm

Construction

- 1.5 & 2.0 mm sheet steel
- 2 4 compartments; other combinations upon request

Load rating

- 1500 kg maximum load rating per frame
- Load rating: 500 kg per compartment; 100 kg per shelf

IP rating

• IP20

Colors

- Standard RAL 7035 and 9005
- · Optionally other colors

Front and rear doors

- Vented door perforation rate 83%
- Swivel handle lock DIN profile, universal key 333, single point;
- Door opening angle 180°
- Easy re-hanging to open on right or left
- Optionally other locks and doors upon request

Side panels

· Removable with locks

Cable entries

- Top and bottom
- All cable entries covered by removable blank panels

19" vertical extrusions


- 2 pairs of sliding 19" vertical L-type (600mm) or C-type (800mm) extrusions for each compartment
- P-type extrusions optional for RSB width 800mm (2 and 3 compartments)

Other

- Racks can be installed in blocks by using DP-DR-UNI (ordered separately)
- GND/earthing kit included
- Individual cabling for each compartment (ordered separately)
- Air separation frame for all compartments (ordered separately)









FOLLOW THE STEPS TO SET UP THE DESIRED RSB RACK PRODUCT CODE!




	HEIGHT	*	
1	Code	Height in U	External height in mm
	42	42	1978
	45	45	2111
	48	48	2245

9	Code	Width in mm
4	60	600
	80	800

	Code	Depth in mm
3	80	800
	100	1000
	120	1200

	NUMBER OF COMPARTMENTS		
	Code	Options	
4	2	2 compartments	
	3	3 compartments	
	4	4 compartments	



^{*} Height in mm without feet

ACCESSORIES		
Code	Description	
RSB-CM-xx ¹ -y ²	Set for individual cable guiding of RSB racks, top or bottom cable entry ³	
DP-RSB-CW-y ² -xx ¹	Set of air separation frames for RSB racks	

¹ Substitute xx with height of RSB rack ² Substitute y with number of compartments

An example of a correct product code

RSB-48-60/100-3-B

³Only RSB 45-2, 42-4 and 45-4 need to define top or bottom cable guiding, add as suffix to the end of code: -T for Top entry, -B for Bottom entry