CONTEG DATASHEET

ACCESSORIES

MOUNTING & CONNECTING KITS

CONTEG, spol. s r.o.

Czech Republic Headquarters:

Na Vítězné pláni 1719/4 140 00 Prague 4

Tel.: +420 261 219 182 Fax: +420 261 219 192

Production plant in the Czech Republic:

K Silu 2179 393 01 Pelhřimov

Tel.: +420 565 300 300 Fax: +420 565 533 955

Local Branches/Offices

Austria: +43 170 659 0115
Benelux: +32 477 957 126
Eastern Europe / Nordics: +49 172 8484 346
France, Maghreb: +33 686 074 386
Germany / Switzerland /

Baltics / Denmark / Italy: +49 170 523 4958 India: +91 99 1695 0773 Middle East: +971 4445 2838 Russia, CIS: +7 495 967 3840

conteg@conteg.com www.conteg.com

MOUNTING & CONNECTING KITS

MOUNTING KIT -

Serves to attach equipment to vertical extrusions

Code	Description	Size	Set includes
DP-MO-01 ¹	Mounting kit	M5	$1\times$ screw, $1\times$ floating nut, $1\times$ washer
DP-MO-F2 ^{1, 2}	Mounting kit – fast installation	M6	1× screw, 1× nut
DP-MO-100	Mounting kit – multipack	M5	100× mounting kit (1× screw, 1× floating nut, 1× washer)

¹Please order in multiples of four only (one packaging = 4 above presented sets)







DP-MO-01



CONNECTING KITS -

Serve to connect (bay) free-standing racks of the same height and depth into one row. The DP-DR-UNI connecting kit is used to connect of the ROF racks series.

- **DP-DR-UNI-Q:** QUICK connecting kit is used to connect all freestanding rack series, excl. iSEVEN series, one-man installation ready, tool-less version
- **DP-DR-UNI:** used to connect of all free-standing rack series, excl. iSEVEN series, side panels do not need to be removed
- DP-DR-7: used to connect of iSEVEN rack series, side panels must be removed



DP-DR-7



Code	Description	Set includes
DP-DR-UNI-Q	${\it QUICK connecting kit for all free-standing rack series, excluding R17 and RM7, tool-less}$	3 brackets of QC, 3 wings screws M5×16, 6 screws M5×16, 3 nuts M5
DP-DR-UNI	Connecting kit for all free-standing rack series, excluding RI7 and RM7	6 wings nuts M5, 6 screws M5×20, 12 washers
DP-DR-7	Connecting kit for RI7 and RM7 rack series	6 hexagonal nuts, 12 screws M5×10, 12 washers M5 DIN125

 $^{^{2}}$ Compatible with cut-out 9.5×9.5 mm